

PREMIUM LO TEMP LAUNDRY DESTAINER

LTD100

TECHNICAL INFORMATION SHEET

PRODUCT DESCRIPTION

LTD100 Premium Lo Temp Laundry Destainer is a specialist, highly advanced concentrated low temperature, coloursafe liquid laundry destainer designed to deliver brilliant cleaning for all your clothing and linen items. Its specially formulated for use in destaining and bleaching with minimal risk of fabric damage and colour fading. Its powerful formulation delivers outstanding results on even the most stubborn of stains and helps to enhance the appearance of fabrics, linens clothes and housekeeping items.

FEATURES AND BENEFITS

- Hypochlorite and Peroxide free formulation
- A high performance advanced low temperature laundry destainer.
- Highly concentrated formula for superior cost in use benefits.
- Enzyme free formulation
- Powerful formula removes the toughest of dirt.
- Delivers outstanding cleaning results.
- Effective for use on all fabric types.
- Suitable for use in front loading or top loading machine types.
- For use through automatic dosing machines and manual dosing systems.
- Ideal for use in large laundries, nursing homes, hospitals and hotels.

INSTRUCTIONS FOR USE

DILUTION

Manual

1. Light Soilage Wash – 4ml - 6.5mls per KG of fabric (Dry Weight).
2. Medium Soilage Wash – 6.6mls - 8.4mls per KG of fabric (Dry Weight).
3. Heavy Soilage Wash – 8.5mls - 15mls per KG of fabric (Dry Weight).



HEALTH & SAFETY



HAZARD AS SUPPLIED:

Causes Eye Irritation.
Wear Gloves for Prolonged Use.

HEALTH & SAFETY



HAZARD WHEN USED:

Causes Eye Irritation.
Wear Gloves For Prolonged Use.

PACK SIZES

SKU	Pack Size
630112	20L

Automatic

1. Light Soilage Wash – Select the correct wash cycle from the auto programmer interface.
2. Medium Soilage Wash – Select the correct wash cycle from the auto programmer interface.
3. Heavy Soilage Wash – Select the correct wash cycle from the auto programmer interface.

Loading the Machine – Manual Use

1. Place the laundry items into the laundry machine paying attention not to overload the laundry machine drum.
2. Make sure the items placed into the laundry machine drum are loosely placed allowing air to distribute around them.
3. Fill the laundry detergent tray with the appropriate measure of LTD100 Premium Lo Temp Laundry Destainer.
4. Select your wash cycle and start the machine.
5. Once the wash cycle has completed, remove the items from the machine wash drum into an appropriate receptacle.
6. Once empty, check the laundry machine drum for any stray laundry items that may have been left behind including any foreign objects such as coins, keys etc.
7. Wipe down the inside of the laundry machine drum and around the door seals with an appropriate disinfectant such as ClearTrace SD50 Broad Spectrum Disinfectant to kill any germs left behind.

Automatic Use

1. Place the laundry items into the laundry machine paying attention not to overload the laundry machine drum.
2. Make sure the items placed into the laundry machine drum are loosely placed allowing air to distribute around them.
3. Select the correct laundry wash cycle from the ClearTrace Automatic Laundry Control System and start the machine.
4. Once the wash cycle has completed, remove the items from the machine wash drum into an appropriate receptacle.
5. Once empty, check the laundry machine drum for any stray laundry items that may have been left behind including any foreign objects such as coins, keys etc.
6. Wipe down the inside of the laundry machine drum and around the door seals with an appropriate disinfectant such as ClearTrace SD50 Broad Spectrum Disinfectant to kill any germs left behind.

SAFE HANDLING AND STORAGE

See visual information on page 1.

Full guidance on the handling and safe use of the product can be obtained from the Safety Data Sheet.

Store in original container.

Avoid extremes of temperature.

TECHNICAL INFORMATION

Appearance:	White liquid.
pH:	2.8 – 3.8.
Odour:	Characteristic.
Solubility:	Fully miscible in water.
Environmental:	100% Bio Degradable.

The above data is typical of normal production and should not be taken as a specification.

MATERIALS COMPATIBILITY

Under recommended conditions of use LTD100 Premium Lo Temp Laundry Destainer is suitable for use on most materials commonly encountered in launderable environments.

OTHER INFORMATION

Always test for colour fastness.

Launder items in line with material type and label.

Not suitable for wool, nylon or fabrics labelled dry clean only.

Not suitable for use with Sodium Sulphite destainer in the same wash.

